


Dräger Quaestor 8000 Test Equipment

All static and dynamic tests of the Dräger Quaestor 8000 are carried out fully automatically. Controlled by the proven Protector software, each test is carried out intuitively. For you, this guarantees high efficiency through comfort and speed.



Benefits

Fully-automatic static and dynamic tests

The test process is fully automated. Automatically opening and closing valves accelerate the process and manual intervention is no longer required. An external microphone also automatically captures the switch-on point of the low-pressure warning. The Quaestor 8000 can read the Dräger Sentinel when equipped with an optional cradle, so that the gauge leveling is done fully automatically.

Comprehensive test options

The Dräger Quaestor 8000 can test full-face masks, chemical protection suits and compressed air breathing apparatus for functionality and leak tightness. Tests of diving apparatus (SCUBA) and closed-circuit breathing apparatus (CCBA) are also possible, if required.

Ergonomic and flexible pressure connections

Dräger's Quaestor 8000 pressure connections are ergonomically and flexibly designed. The medium pressure inlet comes with an extendable hose to eliminate the risk of leaks and resistance due to additional extension hoses. In addition, the rotatable medium pressure outlet reduces the distance between the breathing connection of the lung demand valve and the mask opening or breathing adapter, e.g. if the test head has been rotated by 90 degrees.

Optimum tight fit for all mask sizes

You can turn and remove the test head without restrictions as needed. This flexibility allows you to tailor the test design comfortably to your requirements. In addition, the gel face of the test head, which emulates the elasticity of human facial skin, optimizes a tight fit for all common mask sizes.

Intuitive software

The included software contains a comprehensive database of pre-installed amendable device data. With user notices and graphic elements, the manual test steps are presented comprehensibly even for inexperienced users. After every completed test, a test result report is created for documentation purposes. An optionally applied test-due list provides you with timely information about tests that are due. The software also permits a customer-specific design of the test sequences, events and intervals.

New LED status bar

The new LED status bar informs you using different colors when a test is still running and with which result a test has been completed.

Benefits

Smart accessories

Included in delivery are an external microphone for the detection of the acoustic signal of the low pressure warning and a specially designed bracket to ensure a comfortable rest position of the pressure gauge or Dräger Sentinel. Furthermore, a compressed air breathing apparatus holder allows you to comfortably position the device at eye level.

System Components



Dräger PSS® 7000

Before you can protect the lives of others, you have to protect yourself. The Dräger PSS[®] 7000 self-contained breathing apparatus (SCBA) provides unmatched comfort, durability, and safety in the harshest environments. With unparalleled ergonomic performance, the PSS[®] 7000 combines trusted pneumatics, flexible fit, and cylinder Quick Connection, freeing the firefighter to concentrate on the task at hand.



Dräger PSS[®] BG 4 plus

Specially designed for demanding tasks, The Dräger PSS[®] BG 4 plus closed-circuit breathing apparatus combines uncompromising safety with outstanding respiratory protection and wearer comfort. Innovative in design, it provides the wearer with up to four hours of breathing gas in toxic environments.

System Components



Dräger FPS® 7000

Firefighting requires working under hazardous conditions with poor visibility. Designed to offer optimal visibility, the Dräger FPS 7000 full face mask sets new standards in terms of personal safety, protection and comfort. The popularity of this SCBA mask is due to a large, unobstructed field of vision and a very comfortable and secure fit, while reducing or eliminating fogging during use.

Dräger PSS[®] Lung Demand Valve (LDV)

Suitable for the most extreme applications whenever Breathing Apparatus has to be worn: with its compact and robust design, and excellent pneumatic performance, the Dräger PSS[®] Lung Demand Valve (LDV) will always deliver the air that you need.



D-22691-2009

Dräger CPS 5900

The Dräger CPS 5900 is the ideal limited-use, gas-tight chemical protective suit for hazmat incidents. Where complete protection against hazardous gases, liquids and particles is of the utmost priority, this lightweight garment is the suit of choice.

Accessories



Dräger QSI-Box

Used for sound insulation of the low pressure warning

Compressed Air Breathing Apparatus Holder

Used to position the compressed air breathing apparatus upright during the test



D-6657-2010

Hose for CPS-Test

Necessary accessory for the automatic testing of a chemical protective suit.



Filling nozzle

Minimess[®] (f) - 8 mm, complete

Minimess[®] is a trademark owned by Hydrotechnik GmbH.

Related Products



Dräger Testor 2500

The Dräger Testor 2500 is a compact, versatile test unit for the static tests of your breathing protection equipment. Testing is reliable, easy, and convenient. The compact design enables it to be integrated smoothly into any breathing protection workshop.

Dräger RZ 7000

Easy to use: With the Dräger RZ 7000 you can carry out the function and leak tests of the Dräger PSS $^{\circ}$ BG 4 plus easier and faster than ever before.



D-38692-2015

Technical Data

Permitted temperature (operation) from 0 °C to 40 °C / 32 °I Permitted air pressure 800 to 1.200 hPa / 22.6 ti Permitted humidity 30 to 90 % rel. humidity Compressed air supply Buffer bottle or pipework Pressure sensor accuracy Class ≤ 1.0 according to Pressure ranges High pressure 0350 ba Medium pressure 0430 m Low pressure -40+30 m Low pressure -70+30 m Flow O2 for 1 - 3 l/min (0 External cable connections 1 x USB interface to the F I x 24 V power adapter for 1 x connection for externa 5 to 40 strokes/min
Permitted temperature (operation) from 0 °C to 40 °C / 32 °I Permitted air pressure 800 to 1.200 hPa / 22.6 I Permitted humidity 30 to 90 % rel. humidity Compressed air supply Buffer bottle or pipework Pressure sensor accuracy Class ≤ 1.0 according to Pressure ranges High pressure 0350 ba Medium pressure 0430 m Low pressure -40+30 m Low pressure -70+30 m Flow O ₂ for 1 - 3 l/min (0.1 x USB interface to the F 1 x 24 V power adapter for 1 x connection for external 5 to 40 strokes/min
Permitted air pressure 800 to 1.200 hPa / 22.6 t Permitted humidity 30 to 90 % rel. humidity Compressed air supply Buffer bottle or pipework Pressure sensor accuracy Class ≤ 1.0 according to Pressure ranges High pressure 0350 ba Medium pressure 0430 m Low pressure -40+30 m Low pressure -70+30 m Flow O ₂ for 1 - 3 l/min (0 External cable connections 1 x USB interface to the F I x 24 V power adapter for 1 x connection for externa 5 to 40 strokes/min
Permitted humidity 30 to 90 % rel. humidity Compressed air supply Buffer bottle or pipework Pressure sensor accuracy Class ≤ 1.0 according to 1 Pressure ranges High pressure 0350 ba Medium pressure 0430 m Low pressure -40+30 m Low pressure -70+30 m Flow O ₂ for 1 – 3 l/min (d External cable connections 1 x USB interface to the F I x 24 V power adapter for 1 x 24 V power adapter for 1 x connection for external Breathing frequency of the artificial lung 5 to 40 strokes/min
Compressed air supply Buffer bottle or pipework Pressure sensor accuracy Class ≤ 1.0 according to I Pressure ranges High pressure 0350 ba Medium pressure 0430 m Low pressure -40+30 m Low pressure -70+30 m Flow O2 for 1 – 3 I/min (0 External cable connections 1 x USB interface to the F I x 24 V power adapter for 1 x 24 V power adapter for 1 x connection for external Breathing frequency of the artificial lung 5 to 40 strokes/min
Pressure sensor accuracy Class \leq 1.0 according to Pressure ranges High pressure 0350 ba Medium pressure 025 th Low pressure -40+30 m Low pressure -70+30 m Flow O ₂ for 1 – 3 l/min (0 External cable connections 1 x USB interface to the F I x 24 V power adapter for 1 x 24 V power adapter for 1 x connection for external Breathing frequency of the artificial lung 5 to 40 strokes/min
Pressure ranges High pressure 0350 ba Medium pressure 025 t Low pressure -40+30 m Low pressure -70+30 m Flow O2 for 1 - 3 l/min (0 External cable connections 1 x USB interface to the F Breathing frequency of the artificial lung 5 to 40 strokes/min
Breathing frequency of the artificial lung
Low pressure -40+30 m Low pressure -70+30 m Low pressure -70+30 m Flow O ₂ for 1 - 3 l/min (0 External cable connections 1 x USB interface to the F 1 x 24 V power adapter for 1 x connection for external Breathing frequency of the artificial lung
Low pressure -70+30 m Flow O2 for 1 - 3 l/min (0 External cable connections 1 x USB interface to the F 1 x 24 V power adapter for 1 x connection for external Breathing frequency of the artificial lung
Flow O2 for 1 - 3 l/min (0 External cable connections 1 x USB interface to the F 1 x 24 V power adapter fo 1 x connection for external Breathing frequency of the artificial lung
External cable connections 1 x USB interface to the F 1 x 24 V power adapter fo 1 x connection for externa Breathing frequency of the artificial lung 5 to 40 strokes/min
Breathing frequency of the artificial lung 1 x 24 V power adapter fo 1 x connection for externa 5 to 40 strokes/min
Breathing frequency of the artificial lung 1 x connection for external 5 to 40 strokes/min
Breathing frequency of the artificial lung 5 to 40 strokes/min
Menimum breathing values
Maximum breatning volume 136 1/min
Tidal Volume max. 3.4 I

Ordering Information

Scope of performances		
Dräger Quaestor 8000 Standard NA	PC-supported fully-automatic test instrument for the testing of full-face masks, chemical protection suits and compressed air breathing apparatus	R 63 260
Dräger Quaestor 8000 CCBA NA	PC-supported fully-automatic test instrument for the testing of full-face masks, chemical protection suits, compressed air breathing apparatus and closed circuit breathing apparatus	R 63 290
Filling nozzle cpl., Minimess [®] (f) – 8 mm		37 17 557
Minimess [®] hose 1.5 m (female-female)		37 17 558
For the version Minimess® hose 37 17 558	one of following HP adapters must be ordered	d additionally:
HP adapter 4500 psi, Minmiess (male) -		37 17 565
CGA 347		
HP adapter 300 bar,		37 17 567
Minimess [®] (AG) – 8 mm		

Ordering Information

Dräger QSI-Box	Used for the sound insulation of the low pressure warning	R 58 382
Compressed air breathing apparatus	Used to position the compressed air	37 16 663
holder	breathing apparatus upright during the test	
Hose set CPS test (suits with 2 valves)		R 61 888
Hose set CPS test (suits with 1 valve)		R 61 889
Barcode-label 30 x 13mm (outside)		AG 02 395
Barcode-label 30 x 13mm (inside)		AG 02 396
Barcode-label 22 x 8mm (outside)		AG 02 551
Transponder reader		65 59 283

Minimess[®] is a trademark owned by Hydrotechnik GmbH.

2216 Module	R 58 368
4500 psi Outlet	37 23 208
2216 psi Outlet	37 23 207
Pressure Reducer	R 57 584

Not all products, features, or services are for sale in all countries. Mentioned Trademarks are only registered in certain countries and not necessarily in the country in which this material is released. Go to www.draeger.com/trademarks to find the current status.

CORPORATE HEADQUARTERS

Drägerwerk AG & Co. KGaA Moislinger Allee 53–55 23558 Lübeck, Germany www.draeger.com

USA

Draeger, Inc. 7256 S. Sam Houston Parkway W., Suite 100 Houston, TX 77085 1 800 4DRAGER (1 800 437 2437)

CANADA

Draeger Safety Canada, Ltd. 2425 Skymark Ave., Unit 1 Mississauga, Ontario L4W 4Y6 1 877 DRAGER1 (1 877 372 4371)

Locate your Regional Sales Representative at: www.draeger.com/contact

