

COMBINATION INSTALLATIONS

Document # PGCI - 018


Revised 11/19/09 Page 1/1



Microwave/Discovery Wall Oven/ Warming Drawer

PLANNING GUIDE

All tolerances: +1/16", -0, (+1.6 mm, -0) unless otherwise stated



**CUTOUT DIMENSIONS
DMT2420 SHOWN**




NOTE:

1. 3/4" (19 mm) support platform (flush with cutout).
2. See individual appliance Planning Guide pages to determine overlays.
3. Spacing between appliances and drawers/doors shown is minimum required to allow for ventilation and prevent scraping. Additional space may need to be added for appearance.
4. Warming drawer model OWD24 is not approved for installation above, below or adjacent to a wall oven or another warming drawer (any type).



WARNING

- Observe all governing codes and ordinances during planning and installation. Contact your local building department for further information.
- All appliances must be installed in accordance with the accompanying installation instructions.



**CUTOUT DIMENSIONS
DCM24 SHOWN**

Microwave Model No.	(A) Cutout Width
DMT2420 w/AOMTK series trim kit	24 3/8" (619 mm)
DCM24 w/AOCTK27 trim kit	25 1/4" (641 mm)
DCM24 w/AOCTK30 trim kit	25 1/4" (641 mm)

Wall Oven Models	(B) Cutout Width
Single 27"	25 1/2" (648 mm)
Single 30"	28 1/2" (724 mm)

Warming Drawer Models	(C) Cutout Width
27"	25 1/2" (648 mm)
30"	28 1/2" (724 mm)